

Tehnički list za artikl: HSELS48SCP

Opt. razdjelnik, 48 niti, SC, 50/125µm OM5, 19", 1U, klase C

optički završeci uključeni, 19", 1U, RAL7035, klase C prema IEC 61753-1, CLASSIC



Schrack-Info

These spliceboxes are delivered assembled with already installed couplers and enclosed pigtails (all connectors come with ceramic ferrule).

The spliceboxes are depth-adjustable using the two 19" brackets.

The spliceboxes have one, two or four splice trays depending on the number of fibres with integral splice organisers for shrink-on splice protectors and is designed for up to 4 cable entries, equipped with one M20 cable entry by default.

Blind covers are used to close off unused cable entry ports.

Two versions for up to 48 fibres in a sliding tray design are available:

- with 24 LC-Duplex couplers
- with 24 SC-Duplex couplers
- Material: zinc-coated steel
- Installation: 19", 1U
- Dimensions W x H x D: 483 x 44 x 240mm
- Housing color: RAL7035 Light grey
- Color of couplers (LC and SC): Lime-green
- Dustcovers (LC and SC): Included

Tehnički podaci

Neto širina (mm)	480,00
------------------	--------

Tehnički podaci - nastavak

Neto visina (mm)	44,00
Neto dubina (mm)	242,00
Neto masa (kg)	2,53
Vlakno	50/125 OM5 Multimode
Boja	RAL 7035 (svijetlo siva)
Insercijski gubitak tipično (dB)	< 0,2
Prigušenje povratnog toka tipično (dB)	> 35
Min. temperatura okoline (°C)	-10
Maks. temperatura okoline (°C)	70
Broj vlakana	48

Tablica artikla

OPIS	KAT. BROJ
Opt. razdjelnik, 48 niti, SC, 50/125µm OM5, 19", 1U, klase C optički završeci uključeni, 19", 1U, RAL7035, klase C prema IEC 61753-1, CLASSIC	HSELS48SCP
Dodatni pribor	
Optička cjevčica za zaštitu spoja 60mm	HELSP00011
Optička cjevčica za zaštitu spoja 45mm	HELSP00010
Alat za čišćenje optičkih utikača SC, ST, FC i E2000 Pogodno za UPC i APC utikače. Više od 1000 ciklusa čišćenja.	HSELSZT002
Mjerač snage s integriranim laserom (VFL) za optičke spojeve PAŽNJA: ovo je izvor svjetla Laser klase 2. Nikada ne gledajte u izvor. Uvijek koristite pokrov na VFL portu kad nije u uporabi. Preporučujemo uporabu specijalnih naočala za rad s laserskim izvorima svjetla.	HSELSZT003